


## FLLD4016ATHT3

Aliases (LLD4016ATHT3)

KEMET, FLLD4-TH, EMI/RFI Filters, Noise Suppression, 530 VAC, 16 A, 120x115x80mm



Click [here](#) for the 3D model.

Dimensions	
L	120mm NOM
W	115mm NOM
H	80mm NOM
L1	80mm NOM
W1	127.5mm NOM
W2	143mm NOM
J	32mm NOM
K	6.5mm NOM
M (Earth)	Threaded Studs M6

Packaging Specifications	
Packaging	Bulk
Packaging Quantity	1
Typical Component Weight	800 g

General Information	
Series	FLLD4-TH
Style	Chassis Mount
Description	EMI Filter, Chassis Mount, Compact
Features	High Performance
Phase	Three-phase + Neutral
RoHS	Yes
Qualifications	IEC/EN 60939
Terminal Type	Terminal Block

Specifications	
Voltage AC	530 VAC
Rated Frequency	50-60 Hz
Rated Current	16 A (50°C)
Rated Temperature	50°C
Temperature Range	-25/+100°C
Climate Category	25/100/21
Test Voltage DC (P to P)	2250 VDC
Test Voltage DC (P to E)	3000 VDC
Power Loss	6 W (25°C 50 Hz)
Leakage Current	11 mA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.