



Click [here](#) for the 3D model.

Dimensions	
D	40mm NOM
H	50mm NOM

Packaging Specifications	
Packaging	Bulk
Packaging Quantity	1
Typical Component Weight	110 g

General Information	
Series	FNC
Style	Plastic Cylinder
Description	Compact, High Performance
Features	High Performance
RoHS	Yes
Qualifications	UL, CSA
Terminal Type	Faston

Specifications	
Voltage AC	275 VAC
Rated Frequency	50-60 Hz
Rated Current	16 A (40°C)
Rated Temperature	40°C
Temperature Range	-25/+85°C
Climate Category	25/085/21
Test Voltage DC (P to P)	1700 VDC
Test Voltage DC (P to E)	3000 VDC

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.