



General Information

Series	SS17HB
Style	Through-Hole
RoHS	Yes
Miscellaneous	Inductance Measurement Condition: 1kHz 1V KC530 or equivalent.

Specifications

Voltage AC	250 VAC
Inductance	30 mH
Current	300 mA
Temperature Range	-25/+120°C
DC Resistance	2.6 Ohms

Dimensions

L	20mm MAX
T	17.85mm MAX
H	13.8mm MAX
LL	2.5mm +/-0.5mm
S	16mm +/-0.5mm
S1	10mm +/-0.5mm
Wire Size	0.2mm

Packaging Specifications

Typical Component Weight	5.9 g
--------------------------	-------