



Click [here](#) for the 3D model.

Dimensions

A	68mm MIN
B	215mm MIN
D1	Threaded Studs M12

Packaging Specifications

Packaging	Bulk
Packaging Quantity	1

General Information

Series	FLLDU
Style	Feed-Through Filter
Description	Power Feed-Through Filters
Features	Industrial, Medical
RoHS	Yes

Specifications

Voltage AC	230 VAC
Voltage DC	350 VDC
Rated Frequency	50-60 Hz
Rated Current	300 A
Rated Temperature	40°C
Temperature Range	-40/+85°C
Climate Category	40/085/56