

MINITEK® 1.50MM CONNECTOR SYSTEM

Single row

MODULAR AND COMPACT SOLUTION

Minitek® 1.50mm is a secure and space saving solution for devices that enables connector to carry more signal lines in less space. It is designed with a positive locking system and “audible click” for secure mating retention.

- Saves space with a 1.50mm pitch
- Fully isolated terminals prevents terminals from potential damage
- Housing with positive locking ensures secure mating retention
- Polarized mating geometry and “audible click” prevents accidental mismating
- High retention force in housing secures terminals in housings



TARGET MARKETS



FEATURES

- 1.50mm pitch Wire-to-Board
- Fully isolated terminals
- Housing with positive locking
- Polarized mating geometry and "audible click"
- High retention force in housing
- UL94V-0 flammability rated nylon material
- RoHS compliant and Lead-Free
- Halogen-free resin material

BENEFITS

- Reduces PCB footprint; space saving
- Prevents terminals from potential damage
- Ensures secure mating retention
- Prevents accidental mismating
- Secures terminals in housings
- High flammability rating
- Meets health and safety requirements
- Meets environmental requirements

TECHNICAL INFORMATION

MATERIAL

- Insulation: High Temperature Thermoplastic, Natural color, UL94V-0
- Terminal for Crimping: High Current Alloy with Tin plating

MECHANICAL PERFORMANCE

- Terminal Mating/Unmating Force: Refer to product specification
- Durability: 30 mating cycles

APPROVALS AND CERTIFICATIONS

- UL pending

PACKAGING

- Receptacle: Tape/Reel
- Plug Housing: Bag
- Terminal: Reel

ELECTRICAL PERFORMANCE

- Low Level Contact Resistance: 20mΩ max.
- Insulation Resistance: 500MΩ min.
- Voltage Rating: 100VAC/DC
- Current Rating:
 - 2.0A for 24AWG wires
 - 1.5A for 26AWG wires
 - 1.0A for 28AWG wires
- Dielectric Withstand Voltage: 500VAC

PART NUMBERS

Description	Part Numbers
Minitek® 1.5mm vertical SMT receptacle	10135177
Minitek® 1.5mm right angle SMT receptacle	10136353
Minitek® 1.5mm plug housing	10135175
Minitek® 1.5mm plug terminal	10135176

ENVIRONMENTAL

- Operating Temperature: -40°C to +125°C

SPECIFICATIONS

- Product Specification: GS-12-1321, GS-20-0444
- Packaging Specification: GS-14-2471

TARGET MARKETS/APPLICATIONS



Interior Mirror
Telematics
Entertainment System



LCD TV
CCFL Inverter Board
Button Control Panel



Smart Meter
Smart Grid Gateway