



< [Radio 1/4" Range](#)

R.7

1/4" socket 6-points, 7 mm



- HIGH PERFORMANCE - Designed and manufactured for extremely high tightening forces
- OGV® PROFILE - Maximizing the contact between the socket and nut/bolt to preserves fasteners
- NECK-DOWN DESIGN - Facilitating the use in narrow spaces

[View more features](#)

Additional Features

- FINISHING - Bright chrome

Specifications

Diameter

11 mm

Spark Proof

No

Insulated 1000V

No

Wall

Standard

Type of Profile/Imprint

6 point

For Percussion Screwdriver

No

Standards/Norms

EN 3124, ISO 1711-1, ISO 2725-1, NF ISO 1711-1, NF ISO 2725-1

With Joint

No

Finish

Chrome Varnish

Magnetic

No

 [View Less Specifications](#)

Support

WARRANTY

- Lifetime Replacement Guarantee*

If this product becomes defective due to faulty materials or workmanship within its lifetime, we guarantee to replace it free of charge.

*Terms & conditions apply.

[Learn More](#)

SERVICE

With a century-long legacy of excellence and a touch of French sophistication our Service & Support team is here to assist you with any questions or concerns you may have.

[Learn More](#)

SUPPORT MANUAL

Below are the support items.

No Documents Available



Keep Up To Date

Sign up for news, offers and the latest product updates.

First Name

Last Name

Email Address

Country of Residence

