



**Product:** [8723](#)

Audio, Control & Instrument, #22-2pr, PO, Individ. Foil, PVC Jkt, CM

### Product Description

Audio, Control & Instrument Cable, 22 AWG stranded (7x30) tinned copper conductors, polypropylene insulation, twisted pairs, individually Beldfoil® shielded (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

### Technical Specifications

#### Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	2	22 AWG	7x30	TC - Tinned Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PP - Polypropylene	0.009 in (0.23 mm)	0.046 in (1.2 mm)	Black & Red, Green & White

##### Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC	foil-out tape on each pair, one drain wire

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.020 in (0.51 mm)	0.160 in (4.06 mm)

Overall Cable Diameter (Nominal):	0.160 in (4.06 mm)
-----------------------------------	--------------------

#### Electrical Characteristics

##### Electricals

Element	Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Pair(s)	18.2 Ohm/1000ft	18.38 Ohm/1000ft (60.30 Ohm/km)	33 pF/ft (110 pF/m)	62 pF/ft (200 pF/m)	52 Ohm	66%	2.8 Amps per Conductor at 25°C

##### Voltage

<b>UL Voltage Rating</b>
300 V (CM)

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
60°C	-20°C to +75°C

##### Bend Radius

Stationary Min.	Installation Min.

1.6 in (41 mm) 1.6 in (41 mm)

Max. Pull Tension:	42 lbs (19 kg)
Bulk Cable Weight:	17 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CM
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	82723, 87723, 88723

## History

Update and Revision:	Revision Number: 0.574 Revision Date: 12-22-2023
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
8723.0030	Chrome	Reel	30 m	8719605018571	
8723.060100	Chrome	Reel	100 ft	612825214441	
8723.00100	Chrome	Reel	100 m	8719605159229	
8723.00U152	Chrome	UnReel	152 m	8719605018588	
8723.01152	Chrome	Reel	152 m	8719605018601	
8723.00U305	Chrome	UnReel	305 m	8719605018595	
8723.01305	Chrome	Reel	305 m	8719605018632	
8723.060500	Chrome	Reel	500 ft	612825214526	
8723.060U500	Chrome	UnReel	500 ft	612825214434	
8723.02500	Chrome	Reel	500 m	8719605018663	
8723.01610	Chrome	Reel	610 m	8719605018656	
8723.0601000	Chrome	Reel	1,000 ft	612825214458	C
8723.060U1000	Chrome	UnReel	1,000 ft	612825214410	
8723.001000	Chrome	Reel	1,000 m	8719605018564	
8723.011524	Chrome	Reel	1,524 m	8719605018618	
8723.0601640	Chrome	Reel	1,640 ft	612825214496	
8723.0602000	Chrome	Reel	2,000 ft	612825214502	C
8723.060U2000	Chrome	Reel	2,000 ft	612825214427	
8723.013048	Chrome	Reel	3,048 m	8719605018625	
8723.013050	Chrome	Reel	3,050 m	8719605018649	
8723.0603280	Chrome	Reel	3,280 ft	612825214519	C
8723.0605000	Chrome	Reel	5,000 ft	612825214533	C
8723.06010000	Chrome	Reel	10,000 ft	612825214465	C Y
8723.06010001	Chrome	Reel	10,000 ft	612825214472	C
8723.0609999	Chrome	Reel	10,000 ft	612825214540	C Y
8723.06015000	Chrome	Reel	15,000 ft	612825214489	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.