



Product: [8761](#)

Electronic, 2 C #22 Str TC, PE Ins, OS, PVC Jkt, CM

Request Sample

### Product Description

Electronic, 2 Conductor 22AWG (7x30) Tinned Copper, PE Insulation, Overall Beldfoil® Shield, PVC Outer Jacket, CM

### Technical Specifications

#### Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	22 AWG	7x30	TC - Tinned Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PE - Polyethylene	0.017 in (0.43 mm)	0.062 in (1.6 mm)	Black, Clear

##### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.025 in (0.64 mm)	0.175 in (4.45 mm)

Overall Cable Diameter (Nominal):	0.175 in (4.45 mm)
-----------------------------------	--------------------

#### Electrical Characteristics

##### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Max. Current
Pair(s)	18.2 Ohm/1000ft	24 pF/ft (79 pF/m)	47 pF/ft (150 pF/m)	64 Ohm	6 Amps per Conductor at 30°C

##### Voltage

UL Voltage Rating
300 V (CM), 300 V (UL AWM 2092))

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
60°C	-20°C to +60°C

##### Bend Radius

Stationary Min.	Installation Min.
1.8 in (46 mm)	1.8 in (46 mm)

Max. Pull Tension:	27.3 lbs (12.4 kg)
Bulk Cable Weight:	16 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL 1685 UL loading , IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2092
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
Plenum Number:	88761, 87761, 82761

## History

Update and Revision:	Revision Number: 0.535 Revision Date: 02-15-2024
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
8761.00U152	Chrome	UnReel	152 m	8719605018946	
8761.01152	Chrome	Reel	152 m	8719605018960	
8761.00U305	Chrome	UnReel	305 m	8719605018953	
8761.01305	Chrome	Reel	305 m	8719605018977	
8761 060500	Chrome	Reel	500 ft	612825215301	
8761 060U500	Chrome	UnReel	500 ft	612825215240	
8761.01610	Chrome	Reel	610 m	8719605018984	
8761 0601000	Chrome	Reel	1,000 ft	612825215257	C
8761 060U1000	Chrome	UnReel	1,000 ft	612825215233	
8761 0602000	Chrome	Reel	2,000 ft	612825215295	
8761 0605000	Chrome	Reel	5,000 ft	612825215318	C
8761 06010000	Chrome	Reel	10,000 ft	612825215264	C Y
8761 06015000	Chrome	Reel	15,000 ft	612825215288	C Y

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.