



Quality Products. Service Excellence.

Water-Tight with Integrated Hinge R133-134 Series

aluDOOR

NEW



Key Features:

- Modern, premium enclosures with integrated door
- Constructed of diecast aluminum
- Structurally integrated lid hinges
- Hinges provide 100° opening angle
- Captive stainless steel lid screws and threaded inserts
- Available with a flat lid or recessed lid for membranes, keypads, and labels
- Rated IP66 / IP69K with included PUR gasket
- Clip-on design covers to hide appearance of lid screws
- Tough RAL 7016 gray powder coat finish



Gallery



Enclosures With Recessed Lid

Part Number	Length	Width	Height (Including Lid)
R133-090-000	120	90	70
R133-092-000	160	90	70
R133-110-000	140	110	80
R133-112-000	200	110	80
R133-130-000	160	130	80
R133-132-000	220	130	80
R133-150-000	180	150	90
R133-152-000	260	150	90
R133-170-000	200	170	90
R133-172-000	280	170	90

Enclosures With Flat Lid

Part Number	Length	Width	Height (Including Lid)
R134-090-000	120	90	70
R134-092-000	160	90	70
R134-110-000	140	110	80
R134-112-000	200	110	80
R134-130-000	160	130	80
R134-132-000	220	130	80
R134-150-000	180	150	90
R134-152-000	260	150	90
R134-170-000	200	170	90

Part Number	Length	Width	Height (Including Lid)
R134-172-000	280	170	90

Data subject to change without notice

© 2024. Hammond Manufacturing Ltd. All rights reserved.