



Johanson Product Information for S111TVE

Johanson Company: Johanson Technology inc.

Web Page Link:

<https://www.johansontechnology.com/capacitor-kit>

Deprecated P/N: S111TVE

Datasheet Date: 04-10-2024

Thickness (Max): 1.000

Description: Tuning Capacitor Kit, 1111 S42E-Series Capacitors Contains 10 PCS. EACH of the following 1111 capacitor sizes MLCC (pF): 0.5 B, 0.6 B, 0.7 B, 0.8 B, 0.9 B, 1.0 B, 1.0 B, 1.1 B, 1.2 B, 1.3 B, 1.5 B, 2.0 B, 2.2 B, 2.4 B, 2.7 B, 3.0 B, 3.3 B, 3.6 B, 3.9 B, 4.3 B, 4.7 B, 5.1 C, 5.6 C, 6.2 C, 6.8 C, 7.5 C, 8.2 C, 9.1 C, 10 J

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes. 1

Length (Max): 7.000

Width (Max): 5.000

Life Cycle Stage: Active - Production

Packaged Weight (lb) Arm: 0.40

ECCN: EAR99

RoHS Compliance: Yes, RoHS 10/10

REACH: 1

Product Family: Kits

Product Subfamily: Kits, Capacitor, High-Q, Tuning