

# SSL-2J04-G05MR

Industrial Ethernet cables and fieldbus cables



**PLUG CONNECTORS AND CABLES** 

### SSL-2J04-G05MR | Industrial Ethernet cables and fieldbus cables

PLUG CONNECTORS AND CABLES



Ordering information

•	Туре	Part no.
	SSL-2J04-G05MR	6053217

Illustration may differ

Other models and accessories 

www.sick.com/Industrial\_Ethernet\_cables\_and\_fieldbus\_cables

#### Detailed technical data

#### Technical specifications

Accessory group	Plug connectors and cables
Accessory family	Connection cables
Connection type head A	Male connector, M12, 4-pin, straight, D-coded
Connection type head B	Male connector, RJ45, 8-pin, straight
Connector color	Black
Locking nut material	Zinc die-cast, nickel-plated
Tightening torque	0.4 Nm
Cable	5 m, 4-wire, CAT5, CAT5e, PUR, halogen-free
Jacket material	PUR, halogen-free
Jacket color	Green
Cable diameter	6.5 mm
Conductor cross section	4 x 0.34 mm <sup>2</sup>
Shielding	Shielded
Bending radius	
Flexible use	> 5 x cable diameter
Stationary position	> 5 x cable diameter
Reference voltage	
	≤ 50 V
Current loading	1 A
Signal type	PROFINET
Transmission characteristics	CAT5
Data transmission rate	≤ 100 Mbit/s
Torsion force	± 180°
Torsion cycles	1,000,000
Application	Zones with oils and lubricants Robot
Enclosure rating	IP67 (M12), IP20 (RJ45) <sup>1)</sup>
Ambient operating temperature	
Flexible use	-40 °C +80 °C
Stationary position	-40 °C +80 °C
Head	-25 °C +80 °C


<sup>1)</sup> M12.

PLUG CONNECTORS AND CABLES

#### Classifications

ECLASS 5.0	19030312
ECLASS 5.1.4	19030312
ECLASS 6.0	27060304
ECLASS 6.2	27060304
ECLASS 7.0	27060304
ECLASS 8.0	27060304
ECLASS 8.1	27060304
ECLASS 9.0	27060304
ECLASS 10.0	27060304
ECLASS 11.0	27060304
ECLASS 12.0	27060304
ETIM 5.0	EC000830
ETIM 6.0	EC000830
ETIM 7.0	EC003249
ETIM 8.0	EC003249
UNSPSC 16.0901	26121604

#### Dimensional drawing (Dimensions in mm (inch))



## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

### WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

