

YM2D24-200PN4MRJA4

Industrial Ethernet cables and fieldbus cables

PLUG CONNECTORS AND CABLES





Ordering information

Туре	Part no.
YM2D24-200PN4MRJA4	6050685

Other models and accessories -> www.sick.com/Industrial_Ethernet_cables_and_fieldbus_cables

Detailed technical data

Technical specifications

Accessory group	Plug connectors and cables
Accessory family	Connection cables
Connection type head A	Male connector, M12, 4-pin, straight, D-coded
Connection type head B	Male connector, RJ45, 8-pin, straight
Connector color	Black
Locking nut material	Stainless steel (V4A/1.4404)
Tightening torque	0.6 Nm
Cable	20 m, 4-wire, CAT5, CAT5e, PUR
Jacket material	PUR
Jacket color	Black
Cable diameter	Ø 6.7 mm
Conductor cross section	2 x 2 x 0.34 mm ²
Shielding	Shielded
Reference voltage	
	≤ 60 V
Rated impulse voltage	1 kV
Signal type	Ethernet
Transmission characteristics	CAT5
Data transmission rate	≤ 100 Mbit/s
Application	Outdoor
Enclosure rating	IP67 (M12), IP20 (RJ45) ¹⁾
Ambient operating temperature	
Stationary position	-40 °C +80 °C
Head	-25 °C +85 °C


¹⁾ M12.

Classifications

ECLASS 5.0	19030312
ECLASS 5.1.4	19030312
ECLASS 6.0	27060304
ECLASS 6.2	27060304
ECLASS 7.0	27060304

27060304
27060304
27060304
27060304
27060304
27060304
EC000830
EC000830
EC003249
EC003249
26121604

Dimensional drawing (Dimensions in mm (inch))



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

