



Data Sheet AB6505B

Specifications


Parameters	Values	Units	
Resonant Frequency	520±300	Hz	
Resonant Impedance (Max)	1,000	Ohms	
Max Input Voltage	50	Vp-p	
Capacitance (@ 120 Hz)	93,000±30%	pF	
Plate Material	Brass	-	
Storage Temperature	-30 ~ +80	°C	
Operating Temperature	ting Temperature $-20 \sim +70$ °C		
Environmental Compliances	RoHS/REACH	Exempt. 7c-1	


Dimensions





Packaging





Out Box	300mmx200mmx80mm	8x100PCS=800PCS
Carton Box	310mmx210mmx165mm	800PCSx2=1,600PCS

This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited.

©2021, PUI Audio Inc.

Specifications Revisions

Revision	Description	Date
-	RELEASED FROM ENGINEERING	4/14/2016
A	REVISED CAPACITANCE FREQUENCY AND DIMENSIONS	2/14/2020
В	REVISED MAXIMUM INPUT VOLTAGE	12/8/2021

Note:

- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are ± 0.5 mm and angles are $\pm 3^{\circ}$.
- ${\bf 2.} \quad {\bf Specifications \ subject \ to \ change \ or \ with drawal \ without \ notice.}$