

Product information

35 62 145 ESD

Electronics Pliers ESD

DIN ISO 9655 DIN EN 61 340-5



- Improved transmission for increased service life
- Smoothly ground gripping surfaces for damage-free gripping
- Durable, load-optimised design with backlash-free box joint
- High, slim sleeves for fine and comfortable gripping between thumb and index finger
- Low-friction double spring for gentle and even opening
- Mirror-polishing instead of chrome-plating to avoid interference in the circuit with flaking chrome parts
- Edges carefully deburred
- For fine cutting and assembly work, e.g. in electronics and fine mechanics

General

| | |
|-----------------|------------------------------|
| Article No. | 35 62 145 ESD |
| EAN | 4003773089230 |
| Pliers | mirror polished |
| Head | mirror polished |
| Handles | with multi-component grips |
| Weight | 86 g |
| Dimensions | 145 x 74 x 17 mm |
| Standard | DIN ISO 9655 DIN EN 61 340-5 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|---------------------------|---------|
| Jaw length (B) | 34.1 mm |
| Jaw thickness (joint) (D) | 8.5 mm |
| Tips width (E) | 2.5 mm |
| Tips thickness (F) | 1.8 mm |
| Head width (A) | 13.0 mm |
| ESD | yes |

technical change and errors excepted