

Product information

77 42 130 ESD

Electronics Diagonal Cutters ESD

DIN ISO 9654 DIN EN 61 340-5

- For fine cutting work, e.g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Sturdy, zero-backlash box joint
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Handles with two-colour multi-component grips black/grey



General

Article No.	77 42 130 ESD
EAN	4003773089216
Head	mirror polished
Handles	with multi-component grips
Weight	80 g
Dimensions	130 x 69 x 17 mm
Standard	DIN ISO 9654 DIN EN 61 340-5
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities medium hard wire (diameter)	Ø 1.3 mm
Cutting capacities soft wire (diameter)	Ø 0.3 – 1.6 mm
Jaw length (B)	16.2 mm
Jaw thickness (joint) (D)	8.5 mm
Head width (A)	13 mm
Cutting edge length mm (C)	16.2 mm
ESD	yes

technical change and errors excepted