


Data Sheet SMT-1027-S-4-R


**Specifications** 

Parameters	Values	Units
Rated Voltage	3.6	V0-pk
Operating Voltage Range	2.5 ~ 4.5	V0-pk
Current Draw at Rated Voltage	80	mA
Coil Resistance	20 ± 3	Ohms
Minimum SPL @ 10cm	85	dBA
Resonant Frequency	2,700 ± 500	Hz
Housing Material	LCP	-
Terminal Material	Sn Plating	-
Weight	0.6	Grams
Environmental Compliances	RoHS/REACH	-
Storage Temperature	-30 ~ 80	°C
Operating Temperature	-20 ~ 60	°C


# $Measurement\ Method\ {\it (Temp: 5~35~C; Humidity: 45~85\%; Atmosphere: 860~1060hPa)}$




## **Typical Frequency Response**




**Reliability Testing** 




After reliability test, let rest for 4 hours before testing.






# **Dimensions**




Tolerance: ±0.5mm

@2021,1017

### **Recommended Land Pattern**



# **Packaging**



This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited.

©2021, PUI Audio Inc.

**Specifications Revisions** 

Revision	Description	Date
Α	Released from Engineering	11/17/2022

#### Note:

- 1. Unless otherwise specified:
  - A. All dimensions are in millimeters.
  - B. Default tolerances are  $\pm 0.5$ mm and angles are  $\pm 3^{\circ}$ .
- 2. Specifications subject to change or withdrawal without notice.