

SPECIFICATIONS						
PARAMETERS	VALUES	UNITS				
RATED VOLTAGE	12	Vdc				
OPERATING VOLTAGE RANGE	3 ~ 32	Vdc				
RATED CURRENT (MAX)	9	mA				
MINIMUM SPL @ 10 CM	98	dBA				
RESONANT FREQUENCY	2,800 ± 500	Hz				
TONE OR PULSE RATE	SLOW PULSE	1.5 pulse/sec				
OPERATING TEMPERATURE	-20 ~ +60	°C				
STORAGE TEMPERATURE	-30 ~ +60	°C				
HOUSING MATERIAL	ABS	-				
TERMINAL MATERIAL	Sn PLATED BRONZE	-				
WEIGHT	16	grams				


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.

©2003, Projects Unlimited Inc.

REVISION HISTORY						
LTR	DESCRIPTION	DATE	APPROVED			
_	RELEASED FROM ENGINEERING	7/10/2006				
Α	REVISED VOLTAGE RANGE	1/28/2008	B.R.			
В	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	2/25/2008	B.R.			
С	REVISED PIN LENGTH TO 8.5mm	9/25/2015	M.L.			
D	REVISED VOLTAGE RANGE	2/24/2020	M.V.			









NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2011/65/EU COMPLIANT.

UNLESS OTHERWISE		Designed by	Date	Chec	ked by
SPECIFIED: DIMENSIONS ARE IN	SIZE	J.D.	7/10/2006	Е	.P.
MILLIMETERS,					
TOLERANCES ARE ±0.5 AND	A 3		pul.		
ANGLES ARE ±3°.				тм	
AL-4028-P-SP32-R idw		1	uuul	ınc	

AI-4028-P-SP32-R.idw

7/10/2006 2/25/2008 7/10/2006 R.W. AI-4028-P-SP32-R

Date

Drawn Date

Sheet

1/1

Indicator

Approved by

Date