

248 H Recoilless hammer

With hickory handle, with modified, splinter-proof, shatter-proof and wear-resistant polyamide heads. Powder-coated with silver hammer-effect enamel.

Code	No.	L mm	Ø mm		P.UNIT
8728220	248 H-25	305	25	300	6
8868230	248 H-30	330	30	585	6
8868310	248 H-35	335	35	670	6
8868580	248 H-40	360	40	820	6
8868660	248 H-45	365	45	1030	6
8868740	248 H-50	370	50	1180	1
8868820	248 H-60	370	60	1800	1
8728300	248 H-70	370	70	2300	1
8728490	248 H-80	880	80	4000	1
8728570	248 H-100	1000	100	7000	1



248 F Recoilless hammer

With fibreglass handle and secured head, with modified, splinter-proof, shatter-proof and wear-resistant polyamide heads and handy plastic grip. Powder-coated with silver hammer-effect enamel.

Code	No.	L mm	Ø mm		P.UNIT
8724310	248 F-25	290	25	300	6
8867690	248 F-30	295	30	585	6
8867770	248 F-35	310	35	670	6
8867850	248 F-40	315	40	820	6
8867930	248 F-45	320	45	1030	6
8868070	248 F-50	325	50	1180	1
8868150	248 F-60	335	60	1800	1



248 ST Recoilless hammer

With steel tube handle, with modified, splinter-proof, shatter-proof and wear-resistant polyamide heads. Powder-coated with silver hammer-effect enamel.

Code	No.	L mm	Ø mm		P.UNIT
8724070	248 ST-25	270	25	370	6
8828950	248 ST-30	290	30	585	6
8829090	248 ST-35	295	35	670	6
8829170	248 ST-40	300	40	820	6
8829410	248 ST-45	305	45	1030	6
8829250	248 ST-50	310	50	1180	1
8829330	248 ST-60	325	60	1800	1
8724150	248 ST-70	335	70	2400	1



E-248 H Spare handle hickory

Code	No.		P.UNIT
8739690	E 248 H-25	6	10
8739770	E 248 H-30-35	10	10
8739850	E 248 H-40-45	14	10
8739930	E 248 H-50	14	10
8740000	E 248 H-60-70	18	10
8740190	E 248 H-80	81	10
8740270	E 248 H-100	88	10

E-248 Spare head (piece)

Code	No.	Ø mm		P.UNIT
8747790	E 248-20	20	10	1
8747870	E 248-25	25	10	1
8830260	E 248-30	30	18	1
8830340	E 248-35	35	25	1
8830420	E 248-40	40	35	1
8829920	E 248-45	45	45	1
8830500	E 248-50	50	58	1
8830690	E 248-60	60	140	1
8748410	E 248-70	70	131	1
8748680	E 248-80	80	207	1
8748760	E 248-100	100	363	1

228 Wooden mallet

Red beech wood with round handle.

Code	No.	L mm	Ø mm		P.UNIT
8828010	228-60	300	60	324	6
8828280	228-70	340	70	514	6



DIN 7462 A