

SKINMATIC® mounting tools universal

Mounting help for all cable and conduit glands

not subject of
RoHS directive

SKINMATIC® RZ

For quick mounting of cable and hose glands even when cables are already inserted, suitable for all wrench size of spanners stepless from 14 to 33 mm. The SKINMATIC® RZ is made of chromium plated tool steel and has ergonomically designed plastic grips.

Length of pliers: 250 mm

With two expandable clamping ranges (lock positions):

small width
14-22 mm for
M12 - M16
PG 7 - PG11
NPT 3/8"

large width
24 - 33 mm for
M20 - M25
PG13,5 - PG21
NPT 1/2" - 3/4"



Part number	Type	Wrench sizes mm	Overall length mm	Height mm	PU pieces
6179 1260	SKINMATIC® RZ	14 - 33	250	80	1