# YF8U14-000S01MY8A3

Y- and T-connectors

**PLUG CONNECTORS AND CABLES** 



# YF8U14-000S01MY8A3 | Y- and T-connectors

PLUG CONNECTORS AND CABLES



#### Ordering information

Туре	Part no.
YF8U14-000S01MY8A3	2107428

Other models and accessories → www.sick.com/Y-\_and\_T-connectors

CE

## Detailed technical data

#### **Technical specifications**

Accessory family	Y-junctions		
Connection type head A	Female connector, M8, 4-pin, A-coded		
Connection type head B	Male connector, M8, 3-pin, A-coded		
Connection type head C	Male connector, M8, 3-pin, A-coded		
Locking plug connector	Screw connection		
Signal type	Sensor/actuator cable		
Connector material head A	TPU		
Connector material head C	TPU		
Material knurled screw head A	Zinc die-cast, nickel-plated		
Material knurled screw head C	Zinc die-cast, nickel-plated		
Width across flats	9		
Tightening torque	0.4 Nm		
Shielding, head	Unshielded		
Reference voltage	≤ 30 V AC/DC		
Rated impulse voltage	0.8 kV		
Current loading	4 A		
Insulation resistance	100 ΜΩ		
Contamination rating	3		
Overvoltage category	11		
Specific insulation resistance	30 mΩ		
Enclosure rating	IP67		
Ambient operating temperature			
Head	-25 °C +85 °C		
UL File No.	E335179		
Authorizations	CE		
Classifications			

Classifications


ECLASS 5.0	27279201
ECLASS 5.1.4	27279201
ECLASS 6.0	27279201

# YF8U14-000S01MY8A3 | Y- and T-connectors


PLUG CONNECTORS AND CABLES

ECLASS 6.2	27279201
ECLASS 7.0	27279201
ECLASS 8.0	27279201
ECLASS 8.1	27279201
ECLASS 9.0	27440108
ECLASS 10.0	27440108
ECLASS 11.0	27440108
ECLASS 12.0	27440108
ETIM 5.0	EC002585
ETIM 6.0	EC002585
ETIM 7.0	EC002585
ETIM 8.0	EC002585
UNSPSC 16.0901	31163032

#### Dimensional drawing (Dimensions in mm (inch))



## Connection diagram



# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

