

33ft (10m) VESA-Certified Active DisplayPort 1.4 Cable, DP8K DisplayPort Cable w/HBR3, HDR10, MST, DSC 1.2, HDCP 2.2, 8K 60Hz, 4K 120Hz - DP 1.4 Cable M/M

Product ID: DP14A-10M-DP-CABLE



Connect a 4K/8K DisplayPort 1.4-enabled monitor to a source or MST-enabled hub, using this VESA-Certified Active DisplayPort 1.4 Cable. The active signal booster ensures reliable audio and 8K video output at up to 32.8ft (10m) without a DisplayPort repeater and external power source. This active DP 1.4 cable is unidirectional with conveniently labeled connectors for source and display to simplify setup.

For seamless performance and compatibility between DisplayPort-enabled devices, the Active DisplayPort Cable is VESA Certified, for guaranteed DP 1.4 support and backward compatibility with DP 1.3/1.2

This long DisplayPort cable features a flexible TPE outer jacket to reduce wear from corner bends and long cable runs. Robust strain reliefs enable soft and flexible bends, for convenient positioning of the cable. The latching DP connectors are gold plated for improved conductivity and anti-tarnish properties, and attaches securely to the device to prevent accidental disconnection.

This 8K DisplayPort cable supports all DP 1.4 features:

- Resolutions up to 8K 60Hz, 4K 120Hz, 1440p 240Hz with a compatible DP source and display
- HDCP 2.2 support
- High Bit Rate 3 (HBR3) bandwidth of 32.4Gbps
- High Dynamic Range 10 (HDR10)
- Display Stream Compression 1.2 (DSC 1.2)
- Multi-Stream Transport (MST) for daisy-chaining multiple monitors
- 32 Uncompressed Digital Audio Channels
- Backward compatible with 5K 60Hz, 4K 120Hz and previous DP versions

The Active DP Cable is constructed with aluminum-mylar shielding to minimize EMI interference for clear and reliable audio/video output. This VESA-certified DP cable is designed for long-term reliability, and is the ideal solution for setting up boardrooms, video walls, and TV signage.

Certifications, Reports and Compatibility



Applications

Features

- **DESIGNED FOR LONG RANGE:** 10m (32.8ft) Active DisplayPort 1.4 Cable delivers 8K video beyond the length of passive cables; Integrated self-powered signal booster enables consistent performance without the need for a DP booster or external power source
- **THIRD PARTY CERTIFIED:** The Active DP 1.4 Cable is VESA certified for seamless compatibility with DisplayPort devices and reliable performance over longer lengths; When using certified cables, full-feature DisplayPort compatibility is guaranteed
- **DURABLE CONSTRUCTION:** Latching gold-plated connectors with robust strain reliefs to prevent accidental disconnects; TPE outer cable jacket is flexible, non-toxic, halogen-free, and RoHS compliant; Shielded cable and connector for enhanced EMI protection
- **VERSATILE INSTALLATION:** This active DP 1.4 cable is unidirectional, with conveniently labeled connectors for source and display; 7.5mm Cable O.D. is identical to passive cables and improves flexibility; VW-1 Fire rated jacket enhances flame resistance
- **SPECS:** Black; 10m (32.8ft); Unidirectional cable; DP8K supports HBR3/HDR10/MST/DSC 1.2/HDCP 2.2; 8K 60Hz, 4K 120Hz, 1440p 240Hz w/DSC; Backward Compatible w/ DP 1.3/1.2; Cable O.D.: 7.5mm; Gold-Plated Connectors; Rugged TPE Jacket w/Aluminum Mylar Shield

Hardware

Warranty	2 Years
Active or Passive Adapter	Active
Connector Plating	Gold
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

Fire Rating	VW-1 Rated
Cable Type	Active Copper Cable
Chipset ID	SPECTRA7 VR8300B0-C-R

Performance

Video Revision	DisplayPort 1.4
Maximum Data Transfer Rate	25.92 Gbps
Maximum Digital Resolutions	8K 60Hz 4K 144Hz
Audio Specifications	DisplayPort - 7.1 Channel Audio
General Specifications	Maximum Bandwidth: 32.4 Gbps
Supported Protocols	DisplayPort 1.4 , DisplayPort 1.2

Connector(s)

Connector A	1 - 20 pin DisplayPort Male
Connector B	1 - 20 pin DisplayPort Male

Special Notes / Requirements

System and Cable Requirements	DSC (Display Stream Compression) technology reduces the bandwidth required to transmit video signals, enabling higher resolutions and faster refresh rates without compromising visual quality
-------------------------------	--

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0%~85% RH

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24/28 AWG

Cable Length	32.9 ft [10.0 m]
Cable OD	0.3 in [7.5 mm]
Product Length	35.4 ft [10.8 m]
Product Width	0.8 in [2.0 cm]
Product Height	0.4 in [1.1 cm]
Weight of Product	1.4 lb [0.7 kg]

Packaging Information

Package Quantity	1
Package Length	9.9 in [25.2 cm]
Package Width	13.0 in [33.0 cm]
Package Height	1.6 in [4.0 cm]
Shipping (Package) Weight	1.4 lb [0.6 kg]

What's in the Box

Included in Package	1 - Active DisplayPort 1.4 8K Cable
---------------------	-------------------------------------

**Product appearance and specifications are subject to change without notice.*