

1-Port 2.5Gbps NBASE-T PCIe Network Card, Intel® I225-V, Single-Port Computer Network Card, Ethernet MultiGigabit NIC, PCI Express Server LAN Card

**Product ID:** PR12GI-NETWORK-CARD




This 2.5 GbE network interface card (NIC) features an Intel I225-V chipset with Intel vPro technology, to enhance performance and data integrity. Variable multispeed options (2.5/1Gbps and 100/10Mbps) enable support for both new and legacy network hardware. Leverage existing Cat5e or CAT6 cabling infrastructure while adding NBASE-T (802.3bz) compatibility for seamless integration.

The PCIe network card leverages Intel vPro technology for remote management and troubleshooting capabilities. Improve bandwidth for data-intensive applications, network sharing, FTP, online or local storage/backup, and the streaming of online content - while reducing network slowdowns. Access up to 2.5GBASE-T speeds over Cat5e (or better) cabling, to maximize existing networks and equipment.

The network interface card connects via an available x1 PCI Express 2.0 (or higher) expansion slot. The card ships in a standard profile bracket and includes a low-profile bracket for installation into small form factor systems and servers. This Ethernet NIC card is compatible with Windows, Windows Server, VMware, and Linux.

This card supports the following advanced features: PXE boot, WoL, VLAN tagging, 9 K jumbo frame, full-duplex, and Intel vPro technology.

## Certifications, Reports and Compatibility



## Applications

- Add high-speed data transfer to a desktop for large file transfers, video streaming, and real-time computing
- Upgrade to 2.5Gbps Ethernet to increase network efficiency in enterprise environments

## Features

- **1-PORT 2.5G ETHERNET CARD:** High-performance PCIe 2.5Gbps network card with Intel I225-V chip; Multi-Gigabit; Leverage existing Cat5e/Cat6 (or better) cabling; NBASE-T compatible (802.3bz); PCI Express 2.0 x1
- **IT MANAGEMENT:** Intel vPro for remote management and troubleshooting; PXE boot enabled for centralized OS deployment and updates; 9K jumbo frame for reduced packet overhead; Remote system boot via WoL; VLAN support for efficient network management
- **BUILD QUALITY:** LAN card features built-in heat sink to keep the controller chip cool for optimal performance, LED indicators for link status/speed, and LAN transformers to maintain signal quality and reduce EMI for reliable communications
- **COMPATIBILITY:** 2.5GBASE-T variable speed options (2.5G/1G/100M/10M) with auto-negotiation; Multi-Gigabit PC network interface card is compatible with Windows, Windows Server, VMware, and Linux; Low-profile bracket included for hardware compatibility
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 2.5Gbps Network Card is backed for two years, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	2 Years
Ports	1
Interface	RJ45 (2.5G Ethernet)
Bus Type	PCI Express
Card Type	Standard Profile (LP bracket incl.)
Industry Standards	IEEE 802.3bz (2.5GBASE-T)  IEEE 802.3ab (1000BASE-T)  IEEE 802.3u (100BASE-TX)  IEEE 802.3i (10BASE-TX)  IEEE 802.1Q (VLAN)  IEEE 802.1p (QoS)  IEEE 802.1AS (AVB)  IEEE 802.1X (WoL)  IEEE P802.3az (EEE)  IEEE 1588 (PTP)   PCI Express Version 2.0
Chipset ID	Intel i350-AM4

---

### Performance

Maximum Data Transfer Rate	2.5 Gbps
----------------------------	----------

Compatible Networks	2.5G/1G/100Mbps/10Mbps
Auto MDIX	Yes
PXE	Yes
Full Duplex Support	Yes
Jumbo Frame Support	9K max.

---

#### Connector(s)

Connector Type(s)	1 - PCI Express x1
External Ports	1 - RJ-45

---

#### Software

OS Compatibility	Windows 10, 11 Windows Server 2019, 2022 Linux 5.8.x and up - LTS Versions only VMware ESXi 7.0
------------------	---

---

#### Indicators

LED Indicators	1 - Top LED Indicator is 1000/100/10Mbps Link Activity  Solid Green: 1000/100/10Mbps  Flashing Green: Activity  1 - Bottom LED Indicator is 2.5Gbps Link /Activity  Solid Green: 2.5Gbps  Flashing Green: Activity
----------------	--

---

#### Power

Power Source	Bus Powered
--------------	-------------

---

#### Environmental

Operating Temperature	5C - 50C (41F - 122F)
Storage Temperature	10C - 70C (14F - 158F)
Humidity	5% - 90% RH

---

#### Physical Characteristics

Color	Black
Product Length	4.8 in [12.1 cm]
Product Width	3.5 in [8.9 cm]

Product Height 0.6 in [1.5 cm]

Weight of Product 3.5 oz [100.0 g]

---

**Packaging Information**

Package Length 5.7 in [14.4 cm]

Package Width 8.3 in [21.2 cm]

Package Height 1.3 in [3.4 cm]

Shipping (Package) Weight 4.4 oz [126.0 g]

---

**What's in the Box**

Included in Package 1 - PCIe Network Card

1 - Low-profile Bracket

1 - Quick-start Guide

---

***\*Product appearance and specifications are subject to change without notice.***