

3ft (1m) UK Laptop Power Cable, BS 1363 to C5 (Clover Leaf), 2.5A 250V, 18AWG, UK Laptop Replacement Cord, Printer Power Cable, Laptop Charger Cord, Laptop Power Brick Cord

Product ID: PXTNB3SUK1M



The PXTNB3SUK1M 1m Laptop Power Cord features one BS 1363 (Type G) UK power plug and one 3-prong C5 connector, making it a suitable replacement cable for an HP, Toshiba or other compatible laptop equipped with a cloverleaf/C5 power connection.

Designed for durability and dependability, this Cloverleaf Power Cord is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Spare/replacement laptop power cable for use with grounded UK power outlets
- Extend the connection distance between your laptop and power outlet by 1m

Features

- **AC POWER CORD:** This 3.3ft (1m) 18AWG (0.75mm²) flexible laptop power cord with BS 1363 and IEC 60320 C5 connectors is suitable for workstation/home office use. Rated to carry 250V at 2.5A.
- **PERFORMANCE AND SAFETY:** Fully molded strain relief for durability and VDE approved connectors. Fire Rating: VW-1. 2 Conductor Notebook Power Cable made from 100% Copper Wire.

- **SPECS:** 3.3ft (1m) UK Computer Power Cable BS 1363 to IEC 60320 C5 18AWG (0.75mm²) 250V 2.5A (Max) Jacket Rating: H03VV-F Jacket Material: PVC Color: Black Temperature Range: 2 to 60 Jacket Dimensions: 3.5x6.8 mm

- **COMPATIBILITY:** AC Power Cord BS 1363 works with UK outlets IEC C5 connector works with most power bricks for laptops/notebooks, monitors, scanners, printers, and more Replacement laptop power supply cable/cord

- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this laptop charger cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

General Specifications	In-plug Fuse Rating: 5A
------------------------	-------------------------

Connector(s)

Connector A	1 - BS 1363 Power (UK)
Connector B	1 - IEC 60320 C5 Power

Power

Input Voltage	250 AC
Input Current	2.5 A

Physical Characteristics

Color	Black
Wire Gauge	0.75mm ²
Cable Length	3.3 ft [1 m]
Product Length	39.4 in [100.0 cm]
Product Width	1.1 in [2.9 cm]
Product Height	0.8 in [2.1 cm]
Weight of Product	5.5 oz [155.0 g]

**Packaging
Information**

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.4 in [1.0 cm]
Shipping (Package) Weight	5.6 oz [160.0 g]

What's in the Box

Included in Package	1 - 1m Laptop Power Cord - 3 Slot for UK - BS-1363 to C5
---------------------	--

****Product appearance and specifications are subject to change without notice.***