



Main

Body type	Standard plug-in
Device short name	C
Series name	Heavy duty

Complementary

Line Rated Current	10 A
AWG Gauge	AWG 22...AWG 12
Body material	Zinc alloy
Cable entry	0.5 in (12.70 mm) NPT conduit entry
Contact code designation	A600 Q600
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Maximum displacement angle	90 °
Pilot light	without pilot lamp
Specificity of operator	Standard pre-travel
Switch actuation	CW
Tilting angle	10 °
Torque Value	4 lbf.in (0.45 N.m)
Tripping angle	4 °

Environment

Ambient air temperature for operation	-20...185 °F (-29...85 °C)
NEMA Degree of Protection	NEMA 1/2/4/6/6P/12/13
Product Certifications	UL listed file E42259 CCN NKCR[RETURN]CSA LR25490 class 3211 03[RETURN]CE

Ordering and shipping details

Category	US10DS121499
Discount Schedule	ODS1
GTIN	785901119050
Returnability	No
Country of origin	US

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither TWSS Holding nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.16 in (25.806 cm)
Package 1 Width	4.00 in (10.16 cm)
Package 1 Length	25.81 in (65.548 cm)
Package 1 Weight	20.00 oz (566.991 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------