

RoHS  
Compliant



## Features

- 5 decades of capacitance ranges from 0.1nF~11.111uF (0.1nF step)
- Slide switches allow easy addition and subtraction of capacitance value
- Binding posts offer simple and secure connections

## Specification

Capacitance ranges	: 0.1nF to 11.111uF (0.1nF steps)
Internal Capacitance	: 0.05nF
Voltage limit	: 50V DC
Connection	: Three (3) binding post
Accuracy	: 5%
Operating conditions temperature	: 0 to 50°C (32 to 122°F)
Humidity	: <80%RH
Dimension	: 140mm × 130mm × 48mm
Weight	: 260g

## Part Number Table

Description	Part Number
Capacitance Decade Box, 140mm × 130mm × 48mm	MP701077

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

multicomp<sup>PRO</sup>