

Actuator

46-
2234.31E0.000

Distribution by
Newark



<https://newark.eao.com/p/46-2234.31E0.000>

Your product:



46-2234.31E0.000 Actuator

FRONT

| | |
|------------------------------|-----------|
| Front bezel material: | Metal |
| Front form: | round |
| Front dimension: | Ø 29,5 mm |
| Front bezel colour: | Silver |

MOUNTING

| | |
|--------------------------|-----------|
| Design: | raised |
| Mounting cut-out: | Ø 22.3 mm |

OPERATING-/INDICATION PART

| | |
|---------------------------|--------------|
| Lens illumination: | illuminative |
| Lens optics: | transparent |
| Lens material: | Plastic |
| Lens shape: | flush |
| Lens colour: | Red |

ELECTRICAL CHARACTERISTICS

| | |
|--------------------------|----|
| Protection class: | II |
|--------------------------|----|

MECHANICAL CHARACTERISTIC

| | |
|-----------------------------|-----------------------------|
| Weight: | 0.033 kg |
| Mechanical lifetime: | 500 000 cycles of operation |

Switching action: Maintained
Tightening torque: 2 ... 3 Nm (17.7 ... 26.6 Lb-in)

AMBIENT CONDITION

Operating temperature: - 25 °C ... + 55 °C
IK front protection: IK03
Shock resistance: 50g, 11ms (EN-IEC 60068-2-27)
IP front protection: IP65
Vibration resistance: 5g f= 2...500Hz (EN-IEC 60068-2-6)
Climate resistance: +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

CERTIFICATE

Conformities: CE
Standards: CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

OTHER

Housing material: Plastic
max. number of switching elements: 6
Short Description: Actuator, Ø 22.3 mm, Ø 29,5 mm, flush, illuminative, Red, Plastic, transparent, round, Silver, Metal, Maintained, IP65, IK03
Housing colour: Black
Dimension drawings:

