

Actuator

46-
2234.31H0.000

Distribution by
Newark



<https://newark.eao.com/p/46-2234.31H0.000>

Your product:



46-2234.31H0.000 Actuator

FRONT

Front form:	round
Front dimension:	Ø 29,5 mm
Front bezel material:	Metal
Front bezel colour:	Silver

MOUNTING

Mounting cut-out:	Ø 22.3 mm
Design:	raised

OPERATING-/INDICATION PART

Lens illumination:	illuminative
Lens colour:	Green
Lens optics:	transparent
Lens shape:	flush
Lens material:	Plastic

ELECTRICAL CHARACTERISTICS

Protection class:	II
--------------------------	----

MECHANICAL CHARACTERISTIC

Switching action:	Maintained
Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)

Weight: 0.033 kg
Mechanical lifetime: 500 000 cycles of operation

AMBIENT CONDITION

Shock resistance: 50g, 11ms (EN-IEC 60068-2-27)
IK front protection: IK03
Operating temperature: - 25 °C ... + 55 °C
Climate resistance: +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)
IP front protection: IP65
Vibration resistance: 5g f= 2...500Hz (EN-IEC 60068-2-6)

CERTIFICATE

Standards: CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508
Conformities: CE

OTHER

Housing material: Plastic
Short Description: Actuator, Ø 22.3 mm, Ø 29,5 mm, flush, illuminative, Green, Plastic, transparent, round, Silver, Metal, Maintained, IP65, IK03
max. number of switching elements: 6
Housing colour: Black
Dimension drawings:

