

Actuator

46-
2231.11G0.000

Distribution by
Farnell



<https://farnell.eao.com/p/46-2231.11G0.000>

Your product:



46-2231.11G0.000 Actuator

FRONT

Front dimension:	Ø 29 mm
Front bezel colour:	Black
Front bezel material:	Plastic
Front form:	round

MOUNTING

Design:	raised
Mounting cut-out:	Ø 22.3 mm

OPERATING-/INDICATION PART

Lens colour:	Yellow
Lens illumination:	illuminative
Lens optics:	transparent
Lens material:	Plastic
Lens shape:	flush

ELECTRICAL CHARACTERISTICS

Protection class:	II
--------------------------	----

MECHANICAL CHARACTERISTIC

Weight:	0.019 kg
Mechanical lifetime:	1 Mio. cycles of operation

Tightening torque: 2 ... 3 Nm (17.7 ... 26.6 Lb-in)

Switching action: Momentary

AMBIENT CONDITION

Vibration resistance: 5g f= 2...500Hz (EN-IEC 60068-2-6)

Climate resistance: +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

IP front protection: IP65

Operating temperature: - 25 °C ... + 55 °C

Shock resistance: 30g, 18ms (EN-IEC 60068-2-27)
50g, 11ms (EN-IEC 60068-2-27)

IK front protection: IK03

CERTIFICATE

Conformities: CE

Standards: CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

Approbations: CSA, EAC, UL

OTHER


Housing colour: Black

Housing material: Plastic

max. number of switching elements: 8

Short Description: Actuator, Ø 22.3 mm, Ø 29 mm, flush, illuminative, Yellow, Plastic, transparent, round, Black, Plastic, Momentary, IP65, IK03

Mounting cut-outs:



Dimension drawings:

