

- PRODUCTS ▾
- DISTRIBUTOR INVENTORY
- INDUSTRIES ▾
- SUPPORT ▾
- NEWS & EVENTS ▾
- ABOUT US ▾

NBPLLNS001PGUNV

Products > Sensors > Pressure Sensors & Transducers > Board Mount Pressure Sensors > Unamplified > Basic NBP Series > **NBPLLNS001PGUNV**

Overview

Basic NBP Series, Uncompensated/Unamplified, gage, leadless SMT LN: single axial barbless port, gel coating, 0 psi to 1 psi.
Basic Board Mount Pressure Sensors: NBP Series–
[View More](#)



Technical Specifications

Series Name	Basic NBP	Measurement Type	Gage
Signal Conditioning	Unamplified	Temperature Compensation	No
Pressure Range	0 psi to 1 psi	Supply Voltage	5 Vdc
Supply Current	1.5 mA typ.	Output	Analog
Output Calibration	No	Port Style	LN: single axial barbless port

[View More](#)

View documents in:

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
Basic Board Mount Pressure Sensors: NBP Series, Uncomp/Unamp	Datasheet	English	1MB
50076346-F-EN: Basic Board Mount Pressure Sensors: TBP Series and NBP Series Installation Instructions	Installation Instructions	English	862KB
Basic Leadless SMT LN highres photo	Photo	--	463KB
Embedded Products in Hospital Applications	Brochure	English	5MB

[View More](#)

Product Features

- Cost-effective
- Small size
- Durable
- Flexible
- Robust
- Honeywell brand

- view all NBPLLNS001PGUNV literature
- view distributor inventory
- sample request
- email support
- get support
- email sales
- find a distributor
- email this page

Applications

Medical:

- Hospital beds
- Oxygen concentrators
- Wound therapy
- Blood pressure monitoring

Industrial:

- HVAC transmitters
- Air movement control
- Environmental control
- Leak detection
- Industrial controls
- Pneumatic controls
- Other commercial applications

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)


[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.