

## Honeywell Sensing and Control

Search



### narrow your search

#### Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6165)
- Switches (9781)
- Wireless (45)

#### Technology

- Control and Instrumentation (890)
- Electromechanical (9307)
- Magnetic (541)
- Platinum thin film (56)
- Thick Film (1372)
- More...

### new products

#### New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site  
WGLA and WPMM  
XYR6000™

[find out more](#)

### white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

### Need help?

[Click here to contact us](#)

### 91MCE16-S1

( Home : Products : Switches » MICRO SWITCH™ Limit Switches » MICRO SWITCH™ Global Limit Switches » 91MCE )



Actual product appearance may vary.

Global Limit Switches Series 91MCE: Side Rotary, Fixed length lever with metal roller, 1NO 1NC Direct Opening Slow Action Break-Before-Make (B.B.M.), 1M Cable - Side Exit

[Sales & Service](#)
[Distributor Inventory](#)

[Overview](#)
[Specs](#)
[Documentation](#)
[Application Notes](#)

#### Product Specifications

Availability	Global
Operating Force (OF)	5.0 N [1.12 lb]
Pretravel (PT)	144374
Overtravel (OT)	144374
Differential Travel (DT)	144374
Actuator	Side Rotary
Lever Type	1.5 in Fixed Length Lever with Metal Roller
Circuitry	1NO 1NC Slow Action, BBM
Ampere Rating	10 A (Thermal)
Supply Voltage	300 Vac/250 Vdc max.
Housing Material	Zinc Die-Cast
Termination Type	Side Exit Cable
Series Name	91MCE
Sealing	IP67; NEMA 1, 4, 12, 13
UL File #	E37138
Expected Mechanical Life	5 Million
Operating Temperature	-25 °C to 85 °C [-13 °F to 185 °F]
Agency Approvals and Standards	cULus, CE, CCC
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Cable Length	1 m

### contacts

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

### meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

### my links

- Login to iCOM
- Login to Rep/AD Portal
- Login to Digital University

### News Center

- Honeywell Introduces TruStability® NSC Series, Uncompensated / Unamplified Board Mount Pressure Sensors
- HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER
- HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION
- HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO
- HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION
- HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT

### MICRO SWITCH Anniversary site