

LSA3K-2C

([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Limit Switches](#) : [MICRO SWITCH™ Heavy-Duty Limit Switches](#) : HDLS)



Series HDLS Non Plug-in: Side Rotary; 1NC 1NO SPDT Snap Action; 0.5 in - 14NPT conduit

[click here to download Hi-Res image](#)

Actual product appearance may vary.

Product Specifications

Availability	Global
Operating Force (OF)	0,45 N m [4 in lb] max.
Pretravel (PT)	15° max.
Overtravel (OT)	60° min.
Differential Travel (DT)	5° max.
Product Type	MICRO SWITCH™ Heavy-Duty Limit Switches
Actuator	Side Rotary
Lever Type	1.5 in to 3.5 in Adjustable Length Lever with front mounted Nylon Rollers (.75 in dia x .25 in wide)
Circuitry	1NC 1NO SPDT Snap Action, Double Break
Ampere Rating	10 A (Thermal)
Supply Voltage	600 Vac and 250 Vdc max.
Housing Material	Zinc Die-Cast
Termination Type	0.5 in - 14NPT Conduit
Housing Type	HDLS Non Plug-in
Series Name	HDLS
Sealing	NEMA 1, 3, 4, 4X, 6, 6P, 12, 13
UL File #	E37138
Operating Temperature	-12 °C to 121 °C [10 °F to 250 °F]
Comment	Lever Included
Agency Approvals and Standards	UL, CE, CSA, CCC. EN60947-1, EN60947-5-1
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Switches
Sealed	Industrial