



HONEYWELL  
PART NUMBER  
1SM2  
PRODUCT CODE  
TWA0200

REV	DOCUMENT	CHANGED BY	CHECK
A	0034444	JA 12OCT07	PSR



NOTE -  
1- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX. DIA. ON .375<sup>±.002</sup> CENTERS.  
2- TERMINALS ARE PLATED FOR SOLDERING.  
3- MIN. EXPECTED MECHANICAL LIFE 10,000 OPERATIONS.

RELEASE NO.:  
-  
REPLACES  
-

CHARACTERISTICS	
OPERATING FORCE	3-5 OZ.
RELEASE FORCE	1 OZ. MIN.
DIFFERENTIAL TRAVEL	.004 MAX.
OVERTRAVEL	.010 MIN.

ELECTRICAL DATA		
CONTACT ARRANGEMENT SPDT		
30 VOLTS DC RATING		
	SEA LEVEL	50,000 FT
INDUCTIVE	3 AMP	2.5 AMP
RESISTIVE	5 AMP	5 AMP
MAXIMUM INRUSH 24 AMP		
APPROVALS	KEMA, CE	5A, 250V ~ T85 1E4
	UL, CSA	5A, 250 VAC ~

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X ± 0.040
ONE PLACE .X ± 0.030
TWO PLACE .XX ± 0.015
THREE PLACE .XXX ± 0.005
FOUR PLACE .XXXX ± 0.0005
ANGLES ± 2
THIRD ANGLE PROJECTION

DRAWN	JA	12OCT07
CHECK	PSR	12OCT07
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

<b>Honeywell</b>			
TITLE <b>SWITCH-BASIC</b>			
SIZE	TYPE	DRAWING NAME	REV
B	I	1SM2	14
SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1