

## 2AC109

( Home : Products : Sw itches : MICRO SWITCH™ Basic Sw itches : Standard Miniature and Subminiature Sw itches : AC )



**AC Series Door Switch, Single Pole Double Throw Circuitry, 15 A at 250 Vac, Rod Actuator, Silver Contacts, Screw Termination**

[click here to download Hi-Res image](#)

Actual product appearance may vary.

### Product Specifications

Switch Type	Door 38,1 mm H x 12,7 mm W x 38,1 mm L [1.5 in H x 0.5 in W x 1.5 in L]
Sealed	No
Ampere Rating	15 A
Circuitry	SPDT
Actuator	Rod
Termination	Screw
Operating Temperature	-18 °C to 82 °C [-65 °F to 180 °F]
Voltage	250 Vac
Contact Type	Silver
Operating Position (OP)	11,50 mm [0.453 in] min.
Free Position (FP)	15,62 mm [0.615 in] max.
Housing Material	Stainless Steel Bracket, Stainless Steel Rod
Weight	34,02 g [.075 lb]
Package Height	39,9 mm [1.57 in]
Package Width	13,2 mm [0.52 in]
Package Length	50,0 mm [1.97 in]
Availability	Global
UNSPSC Code	39122209
UNSPSC Commodity	39122209 Snap sw itches
Series Name	AC