

BM-IR369-A41

CATALOG LISTING



ISSUE

**B**

CHECK

REVISIONS

B 0035412

BS 04DEC07

ASD

CHECK

ASD

CHECK

29 MAY 03

SAV

CHECK

29 MAY 03

SAV

CHECK

29 MAY 03

CHECK

29 MAY 03

CHECK

29 MAY 03


PTC/CAD 2D

DRAWN

PAGE 1 OF 1

REPLACES X115011-BM

RELEASE NO. 0000400



3X 8-32 UNC THREAD  
∇ .172 MIN IN INSERTS  
FOR TERMINAL CONNECTION

NOTE MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF  $\phi .139$  MAX ON 1.000 ± .002 CENTERS

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE	----- 11 - 17 OZ
DIFFERENTIAL FORCE	----- 1 - 5 OZ
DIFFERENTIAL TRAVEL	----- .0001 - .0011
OVERTRAVEL	----- .005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT  
S P D T

L82 22A 125, 250 OR 277 VAC  
1/4HP 125 VAC, 1/2HP 250 VAC

L288  
L315  
L318



22A 250V ~ T85 5E4

SCALE FULL SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0) ± .030

TWO PLACE (.00) ± .015

THREE PLACE (.000) ± .005

ANGLES ±

WEIGHT .063 LB



THIRD ANGLE PROJECTION

DO NOT SCALE PRINT