



NOTE -
 1- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
 OF .139 MAX. DIA. ON 1.000 ±.002 CENTERS.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	
OPERATING FORCE -----	16-26 OZ.
RELEASE FORCE -----	4 OZ. MIN.
DIFFERENTIAL TRAVEL -----	.001 - .004
OVERTRAVEL -----	.219 MIN.

ELECTRICAL DATA	
CONTACT ARRANGEMENT SINGLE POLE DOUBLE THROW SPLIT CONTACT	
-L4- UNDERWRITERS' LAB. INC. LISTED RATING 5 A 250 VAC	

SCALE -----	FULL
DO NOT SCALE PRINT	
UNLESS OTHERWISE SPECIFIED	
DIMENSIONS ARE IN INCHES	
TOLERANCES ARE:	
ONE PLACE (.)	±.030
TWO PLACE (.00)	±.015
THREE PLACE (.000)	±.005
ANGLES	±
WEIGHT -----	.092 LB.

BZ-3YQ66T
M
 DRAWING NUMBER
X 2
5
 ISSUE
X 5
74-86
 DRAWN
D.A.W.
17, JUNE '55
 CHECK
RVK
20, JULY '55
 CHECK
VHS
7, JULY '55
 CHECK
CNT
18, JULY '55
 RELEASE NO.
C.O. 8520
 REPLACES

REVISIONS

A	00-34304	J A L	11 FEB 75
B	00-34304-D	J A L	11 FEB 91
C	00-34304	SAD	11 JUN 94
D	203837	TSM	30 AUG 01