

V7-6C17D8-439

(Home : Products : Sw itches : MICRO SWITCH™ Basic Sw itches : Premium V-Basic Sw itches : V7)



V7 Series Miniature Basic Switch, Single Pole Double Throw Circuitry, 15 A at 250 Vac, Special Straight Steel Actuator, 146 gf Maximum Operating Force, Silver Contacts, Quick Connect Termination

Actual product appearance may vary.

[click here to download Hi-Res image](#)

Product Specifications

Sw itch Type	MICRO SWITCH™ Miniature 15,9 mm H x 10,2 mm W x 28,8 mm L [0.63 in H x 0.4 in W x 1.14 in L]
Sealed	No
Ampere Rating	15 A
Circuitry	SPDT
Actuator	Special Lever
Termination	Quick Connect
Operating Temperature	-40 °C to 82 °C [-40 °F to 180 °F]
Voltage	250 Vac
Actuator Length	44,5 mm [1.75 in]
Contact Type	Silver
Operating Force (OF)	146 gf max.
Release Force	24 gf min.
Pretravel (PT)	5,08 mm [0.20 in] max.
Overtravel (OT)	1,96 mm [0.077 in] min.
Differential Travel (DT)	1,1 mm [0.043 in] max.
Operating Position (OP)	15,3 mm ±0,558 mm [0.603 ±0.022 in]
Housing Material	PCT Polyester Thermoplastic
Agency Approvals and Standards	UL, CSA
Mounting Centers	22,2 mm [0.88 in]
Tightening Torque	0,56 N m [5.0 in lb]
Weight	8 g [0.3 oz]
Package Height	15,9 mm [0.63 in]
Package Width	10,3 mm [0.40 in]
Package Length	27,8 mm [1.09 in]
Comment	CE: 61058-1; UL: E12252; CSA: LR41370
Availability	Global
UNSPSC Code	39122209
UNSPSC Commodity	39122209 Snap sw itches
Series Name	V7