

V7-7B17D8-481

(Home : Products : Sw itches : MICRO SWITCH™ Basic Sw itches : Premium V-Basic Sw itches : V7)



V7 Series Miniature Basic Switch, Single Pole Double Throw Circuitry, 11 A at 250 Vac, Curved Tip Actuator, 178 gf Maximum Operating Force, Silver Contacts, Quick Connect Termination

Actual product appearance may vary.

Product Specifications

Sw itch Type	MICRO SWITCH™ Miniature 15,9 mm H x 10,2 mm W x 28,8 mm L [0.63 in H x 0.4 in W x 1.14 in L]
Sealed	No
Ampere Rating	11 A
Circuitry	SPDT
Actuator	Curved Tip Lever
Termination	Quick Connect
Operating Temperature	-40 °C to 85 °C [-40 °F to 185 °F]
Voltage	250 Vac
Actuator Length	19,4 mm [0.76 in]
Contact Type	Silver
Operating Force (OF)	178 gf max.
Release Force	28 gf min.
Pretravel (PT)	2,16 mm [0.085 in] max.
Overtravel (OT)	1,3 mm [0.051 in] min.
Differential Travel (DT)	0,50 mm [0.020 in] max.
Operating Position (OP)	19,51 mm ±1,02 mm [0.768 ±0.040 in]
Housing Material	PCT Polyester Thermoplastic
Agency Approvals and Standards	UL, CSA
Mounting Centers	22,2 mm [0.88 in]
Tightening Torque	0,56 N m [5.0 in lb]
Weight	8 g [0.3 oz]
Package Height	15,9 mm [0.63 in]
Package Width	10,3 mm [0.40 in]
Package Length	27,8 mm [1.09 in]
Comment	CE: 61058-1; UL: E12252; CSA: LR41370
Availability	Global
UNSPSC Code	39122209
UNSPSC Commodity	39122209 Snap sw itches
Series Name	V7