

- PRODUCTS ▾
- DISTRIBUTOR INVENTORY
- INDUSTRIES ▾
- SUPPORT ▾
- NEWS & EVENTS ▾
- ABOUT US ▾

17AC18-T

[Products](#) > [Switches](#) > [Basic Switches](#) > [Specialty Large Basic Switches](#) > [AC Series](#) > **17AC18-T**

Overview

MICRO SWITCH AC Series Door Switch, Single Pole Double Throw (SPDT), 250 Vac, 5 A, Plunger lever Actuator, Solder Termination. ... [View More](#)



Technical Specifications

Switch Type	Door 30,0 mm H x 9,01 mm W x 42,9 mm L [1.182 in H x 0.355 in W x 1.69 in L]	Ampere Rating	5 A
Sealed	No	Circuitry	SPDT
Actuator	Plunger Lever	Termination	Solder
Operating Temperature	-53 °C to 121 °C [-65 °F to 250 °F]	Voltage	250 Vac
Contact Type	Silver	Overtravel (OT)	4,47 mm [0.175 in] max.

[View More](#)

View documents in:

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
MICRO SWITCH AC Series Door Switches	Datasheet	English	2MB
Basic, Toggles, and Rocker Switches Range Guide	Product Range Guide	English	2MB
Safety and Productivity Solutions in Hospital Applications	Brochure	English	5MB

Product Features

- Automatically cuts power when service door or drawer is opened
- Choice of momentary, maintained or pull-to-cheat actuation
- Versatile mounting bracket for side or end mounting
- Current rating ranges from 5 A to 25 A
- Available with one or two SPDT switches
- UL recognized versions available
- Choice of termination

Applications

- Appliances
- Vending machines

- [view all 17AC18-T literature](#)
- [view distributor inventory](#)
- [sample request](#)
- [email support](#)
- [get support](#)
- [email sales](#)
- [find a distributor](#)
- [email this page](#)

- Office equipment
- Computer/business equipment
- Test instruments
- Medical/dental equipment
- Communications equipment
- HVAC equipment

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)

[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.