

32NT391-7-C08

(Home : Products : basics : Sw itches : MICRO SWITCH™ Toggle Sw itches : NT)



NT Series Toggle Switch, 2 pole, 3 position, Quick Connect terminal, Special Design Lever

Actual product appearance may vary.

Product Specifications

Product Type	MICRO SWITCH™ Toggle Sw itch
Ampere/Voltage Range (Resistive Load)	0.5 A at 250 Vdc 0.75 A at 115 Vdc 0.5 A to 10 A at 0.5 Vac to 277 Vac 0.5 A to 18 A at 0.5 Vdc to 28 Vdc
Circuitry	DPDT
Action	3 position
Circuitry/Operating action	<div style="display: flex; justify-content: space-around; align-items: flex-start;"> <div style="text-align: center;"> <p>Keyway Momentary Position</p> <p>ON</p> </div> <div style="text-align: center;"> <p>Center Position</p> <p>OFF</p> </div> <div style="text-align: center;"> <p>Opposite Keyway Momentary Position</p> <p>ON</p> </div> </div>
Mounting	Bushing 15/32 in
Termination	Quick Connect
Lever Type	Special Design
UL/CSA	L192: 10 A-125, 250, 277 Vac; 1/4 Hp-125 Vac; 1/2 Hp-250, 277 Vac; 3 A-125 Vac "L"
Comment	Yellow
Availability	Global
UNSPSC Code	39122211
UNSPSC Commodity	39122211 Toggle Sw itch
Series Name	NT