



Home

Products

- AC Meters
- DC Meters
- LCD Meters
- Battery Discharge Indicators
- Work Lamps
- Pressure/Vacuum Switches
- Flashers

Technical Support

- FAQs
- Customer Service

OEM Applications

www.hobbscorporation.com

Featured Product

INCREASE YOUR BATTERY LIFE
with Hobbs' NEW Battery Discharge Indicators

Model 826
for more information [click here](#)

Invensys Sensor Systems is now a part of **Honeywell Sensing and Control** - the world's largest single source supplier of sensors and switches.

Our expanded product offering includes:

- Sensors**
- Automotive On -Board
- Current Sensors
- Fiber Optic Sensors
- Force Sensors
- Humidity Sensors
- Infrared Products
- Liquid Level Sensors
- Mass Airflow Sensors
- Moisture Sensors
- Position Sensors
- Pressure Sensors
- Proximity Sensors - Aerospace/Military/Transportation
- Rail Products
- Temperature Sensors
- Thermocouples, Non -contact Probes and RTDs
- Turbidity Sensors
- Ultrasonic Sensors

Switches

- Basic Switches
- Environment Sealed Switches
- Indicators
- Keypswitches
- Limit and Enclosed Switches
- Pushbuttons
- Relays
- Rocker Switches
- Thermal Switches
- Toggle Switches

Safety Products for Machine

- Safeguarding
- Safety Modules
- Safety Sensors
- Safety Switches

Wintriss Safety Products

ac meters

Specifications:

- ? Polycarbonate, shock resistant, tamper proof case
- ? Records up to 99,999 hours Automatic recycle to zero
- ? Screw Terminal Meters Totally Sealed
- ? Single phase, synchronous, permanently lubricated motor
- ? 24, 120 and 240 VAC models available (Range $\pm 10\%$)
- ? 50 and 60 Hertz versions
- ? 3.0 watts power rating
- ? Operating temperature: - 65°F to +154°F, (- 54°C to +68°C)
- ? Accuracy: $\pm .02\%$
- ? Weight: 3 oz
- ? Screw termination or 7" lead wires
- ? Lens material: 3 - screw mount: Glass All others: Polycarbonate
- ? Case material: Polycarbonate
- ? Number size: 0.12" (3mm)
- ? UL Listed (File# E47098): Screw terminals
- ? UL Recognized: Wire lead versions
- ? CSA Certified (File# LR42455)
- ? Conforms to MIL - M - 3971

Find a direct replacement for obsolete or unlisted Hobbs meters or competitor meters:

Enter part number or partial part number entering at least first three digits

AC Meter Wiring Diagrams

AC Meter Accessories



Dimensions

Panel cutout 1.45 x .95 rectangular opening. Two .150 holes spaced 1.750.

Rectangular 2 Screw

Operating Voltage	Hertz	Termination	Part Number
22 to 26 VAC	60	Screw*	20085
108 to 132 VAC	50	Screw*	20028
108 to 132 VAC	60	Screw*	20001
108 to 132 VAC	60	7" Leads**	20035
216 to 264 VAC	50	Screw*	20029
216 to 264 VAC	50	7" Leads**	20036
216 to 264 VAC	60	Screw*	20007
216 to 264 VAC	60	7" Leads**	20037

* UL Listed & CSA Certified

**UL Recognized & CSA Certifies



Dimensions

Panel cutout 2.00 diameter opening. Three .125 holes equally spaced on 2.42 bolt circle diameter.

Round 3 Screw

Operating Voltage	Hertz	Termination	Part Number
108 to 132 VAC	50	Screw*	20016
108 to 132 VAC	60	Screw*	20017
216 to 264 VAC	50	Screw*	20018
216 to 264 VAC	60	Screw*	20019

* UL Listed & CSA Certified

**UL Recognized & CSA Certifie



Dimensions

Panel cutout 1.45 x .95 rectangular opening.

Rectangular 2 Screw

Operating Voltage	Hertz	Termination	Part Number
108 - 132 VAC	60	Screw*	20116 -23

* UL Listed & CSA Certified