

Fluke Combo Kits

A kit for whatever job you do

We've asked our test-tool users in the three main fields (industrial, electronic and electrical) what they use most and have assembled the kits to provide the optimum mix of our top-selling products. All provide you with a considerable saving on the price of buying each item individually.

Industrial Combo Kit

Buy
Combo Kit
and Save
17%

Fluke 179 True RMS Multimeter

- True RMS measurements
- 0.09% Basic DC accuracy
- 6000 count digital display with analog bargraph and backlight
- Min-Max-Average recording
- Frequency and capacitance measurements
- Temperature measurement

TL224 SureGrip™ Silicone Test Lead Set

- 1.5 m test leads (red, black) with safety shrouded standard diameter banana plugs

AC220 SureGrip™ Alligator Clip Set

- One pair (red, black) of small insulated jaws, open up to 9.5 mm

TP4 Slim Reach Test Probe Set (4 mm)

- One pair (red, black) for probing closely spaced or recessed terminals

80BK Integrated DMM Temperature Probe

- Type-K thermocouple with standard banana jack

C800 Hard Meter and Accessory Case

+ Maglite flashlight



Buy
Combo Kit
and Save
24%

Electronics Combo Kit

Fluke 179 True RMS Multimeter

- True RMS measurements
- 0.09% Basic DC accuracy
- 6000 count digital display with analog bargraph and backlight
- Min-Max-Average recording
- Frequency and capacitance measurements
- Temperature measurement

TL224 SureGrip™ Silicone Test Lead Set

- 1.5 m test leads (red, black) with safety shrouded standard diameter banana plugs

TL910 Electronic Test Probe Set

- Very small 1 mm tips to access hard to reach test points with replaceable steel and spring loaded gold tips.

AC280 SureGrip™ Hook Clip Set

- One pair (red, black). Profile narrows to 5.6 mm at tip, hook opening 6.4 mm at front, 2 mm at base

80BK Integrated DMM Temperature Probe

- Type-K thermocouple with standard banana jack

C800 Hard Meter and Accessory Case



Electrician's Combo Kit

Fluke 112 True RMS Multimeter

- True RMS measurements
- 0.7% Basic DC accuracy
- 6000 count digital display with analog bargraph and backlight
- Min-Max-Average recording
- Frequency and capacitance measurements
- Compact case with removable holster

Fluke 322 Clamp Meter

- 1.8% AC current accuracy
- 400 A AC range
- Voltage AC/DC measurements
- Jaw opening 25 mm

TL76 All-in-one Test Lead Set

- One pair (red, black) 1.5 m long silicone test leads with removable 2 mm and 4 mm lantern tips

C800 Hard Meter and Accessory Case

Buy
Combo Kit
and Save
23%



FLUKE®

189/FlukeView Combo Kit

Buy
Combo Kit
and Save
16%



Fluke 189 True RMS Multimeter

- AC and AC+DC True RMS measurements
- 0.025% basic DC accuracy
- 50,000 count multiple readings digital display with analog bargraph and backlight
- Temperature and dB measurements
- Memory for up to 3 days continuous stand-alone logging
- Infrared PC interface for data exchange with computers

FVF-SC2 FlukeView Forms Software

- Connect the Fluke 189 to a computer for downloading, logging, storing and analyzing measuring data.

179/ToolPak Combo Kit

Fluke 179 True RMS Multimeter

- True RMS measurements
- 0.09% Basic DC accuracy
- 6000 count digital display with analog bargraph and backlight
- Min-Max-Average recording
- Frequency and capacitance measurements
- Temperature measurement with included bead probe

TPAK, ToolPak Meter Hanging Kit

- Keep both hands free to move the test leads around



Buy
Combo Kit
and Save
7%

Fluke. *Keeping your world up and running.*

Ordering Information

Fluke 179/MAG Kit	Industrial Combo Kit
Fluke 179/EDA Kit	Electronics Combo Kit
Fluke 112/322 Kit	Electrician's Combo Kit
Fluke 179/ToolPak	179/ToolPak Combo Kit
Fluke 189/FVF	189/FlukeView Combo Kit

Fluke Corporation
P.O. Box 9090
Everett, WA USA 98206

Fluke Europe B.V.
P.O. Box 1186
5602 BD Eindhoven
The Netherlands

For more information call:
In the U.S.A. (800) 443-5853
or Fax (425) 446-5116
In Europe/M-East/Africa +31 (0)40 2 675 200
or Fax +31 (0)40 2 675 222
In Canada (905) 890-7600
or Fax (905) 890-6866
From other countries +1 (425) 446-5500
or Fax +1 (425) 446-5116
Visit us on the world wide web at:
<http://www.fluke.com>

Fluke (UK) Ltd.
52 Hurricane Way
Norwich
Norfolk
NR6 6JB
United Kingdom
Tel.: 0207 942 0700
Fax: 0207 942 0701
E-mail: industrial@uk.fluke.nl
Visit us on the world wide web at:
<http://www.fluke.co.uk>

© Copyright 2003 Fluke Corporation. All rights reserved.
Printed in the Netherlands 01/03.
Data subject to alteration without notice.

Pub ID: 10582-eng
Rev. 01