

ICC20 Backshell straight (17-20,5 mm)



Image is for illustration purposes only. Please refer to product description.

Part number	19 59 120 4013
Specification	ICC20 Backshell straight (17-20,5 mm)
HARTING eCatalogue	https://b2b.harting.com/19591204013

Identification

Category	Connectors
Series	HARTING ICC
Type of hood/housing	Backshell
Description of hood/housing	With integrated cable gland Straight

Version

Size	20
Version	Top entry

Technical characteristics

Tightening torque	12 Nm Cable gland 15 Nm Backshell
Limiting temperature	-40 ... +125 °C
Number of relockings	≥10
Degree of protection acc. to IEC 60529	IP67 IPX9
Clamping range	17 ... 20.5 mm

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (seal)	TPE
Colour (seal)	Brown



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
Approvals	CE

Commercial data

Packaging size	1
Net weight	0.071 kg
European customs tariff number	85389099
GTIN	5713140400597
eCl@ss	27440224 Shell for circular connectors