

BU-2020SR-A-XX-@

(TEST LEAD, STACKABLE 4MM BANANA PLUGS, 19A, W/ STRAIN RELIEF)



- The BU-2020SR is a double ended test lead that includes a standard 4mm stackable banana plug on each end. It features a strain relief on the connector to provide extra support for the wire.
- Uses 16AWG PVC wire.
- Length is designated in inches by the “XX” in the part number.
Available lengths are: 12”, 24”, 36”, 48” and 60”
- Ratings:
 - Operating Voltage: 30Vac-60Vdc
 - Current: 19 Amps
- Color: The “@” in the model number represents color. Available colors:
-0 Black, -2 Red
- RoHS 3 Compliant, CE Certified