



## S800



### 1/4" and 1/2" Square Drive Spanner and Socket Set



#### PRODUCT DETAILS

- 12-Piece 1/4" hex sockets 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12 and 13 mm
- Nine 1/4" deep hex sockets: 4-13 mm
- Two 1/4" extension bars: 50 mm and 100 mm
- One 1/4" sliding T-handle, 106 mm
- One 1/4" universal joint
- One 1/4" spinner handle, 150 mm
- One 1/4" reversible ratchet, 150 mm
- Four 1/4" Phillips socket drivers, PH1, PH2, PH3 and PH4
- Three 1/4" flat socket drivers 4, 5.5 and 7 mm
- Six 1/4" hex socket drivers, 3, 4, 5, 6, 8 and 10 mm
- Three hexagon L-keys: 1.5, 2 and 2.5 mm
- 15-Piece 1/2" hex sockets 10-34 mm
- Nine 1/2" hex sockets AF: 3/8, 7/16 (11), 1/2, 9/16, 11/16, 3/4 (19), 13/16, 7/8 (22) and 1-3/16"
- Four 1/2" hex sockets, 17, 19, 21 and 24 mm
- Two 1/2" extension bars, 125 mm and 250 mm
- One 1/2" universal joint
- One 1/2" hex spark plug socket: 21 mm
- One 1/2" sliding T-handle, 3/8" female - 1/2" male, 3 ways
- One 1/2" reversible ratchet, 250 mm
- Matte finish
- High-performance alloy steel
- Less wear and damage to fastener thanks to Dynamic-Drive™ profile sockets
- Quick socket release button on ratchet
- Case: High density polythene (HDPE)
- Standards: ISO 1174 and DIN 3120

#### PRODUCT ATTRIBUTES

Product				
<b>S800</b>	430 mm	375 mm	110 mm	7340 g

Follow the Fish!

