



Part Number : 173310406

**Product Description** : 0.50mm Pitch Premo-Flex FFC Jumper with Ears, Same Side Contacts (Type A), 102.00mm Cable Length, Gold (Au) Plating, 6 Circuits

Series Number : 17331

**Status** : Active

**Product Category** : Flexible Printed Circuit (FPC) Flex Jumpers

---

## Documents & Resources

### Drawings

Drawing 173310406\_sd.pdf


### Specifications

Product Specification 173310001-001.pdf

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

Status	Active
Category	Flexible Printed Circuit (FPC) Flex Jumpers
Series	17331
Description	0.50mm Pitch Premo-Flex FFC Jumper with Ears, Same Side Contacts (Type A), 102.00mm Cable Length, Gold (Au) Plating, 6 Circuits
Comments	Contacts on the same side, Type A
Product Family	FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Product Name	Premo-Flex FFC Jumper
UPC	198282267744

### Electrical

Current - Maximum per Contact	0.55A
Voltage - Maximum	60V AC

### Physical

Cable Length	102.00mm
Circuits (Loaded)	6
Contact Layout Type	A (same side)
Design Feature	Superior Retention
Material - Plating Mating	Gold
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	Flat Flex Cable
Wire Size (AWG)	N/A

---

## Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Intermateable with Hirose TF31

---

This document was generated on Jul 01, 2024