



Part Number : [173520320](#)

Product Description : 0.50mm Pitch Premo-Flex FFC Jumper with Ears, Same Side Contacts (Type A), 76.00mm Cable Length, Gold (Au) Plating, 20 Circuits

Series Number : 17352

Status : Active

Product Category : Flexible Printed Circuit (FPC) Flex Jumpers

---

## Documents & Resources

### Drawings

[Drawing 173520320\\_sd.pdf](#)


### Specifications

[Product Specification 173520001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

Status	Active
Category	Flexible Printed Circuit (FPC) Flex Jumpers
Series	17352
Description	0.50mm Pitch Premo-Flex FFC Jumper with Ears, Same Side Contacts (Type A), 76.00mm Cable Length, Gold (Au) Plating, 20 Circuits
Comments	Contacts on the same side, Type A
Product Family	FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Product Name	Premo-Flex FFC Jumper
UPC	198282268017

### Electrical

Current - Maximum per Contact	0.55A
Voltage - Maximum	60V AC

### Physical

Cable Length	76.00mm
Circuits (Loaded)	20
Contact Layout Type	A (same side)
Design Feature	Superior Retention
Material - Plating Mating	Gold
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	Flat Flex Cable
Wire Size (AWG)	N/A

---

### Mates With / Use With

## Mates with Part(s)

Description	Part Number
Mates With	Intermateable with Hirose FH52

---

This document was generated on Jul 01, 2024