

PNOZ X3 110VAC 24VDC 3n/o 1n/c 1so

774314



Safety relay (standalone), inputs: 1/2-channel wiring with/without detection of shorts across contacts, outputs: 3 N/O, 1 N/C, 1 SC, automatic/monitored start, UB 110 V AC/24 V DC, width: 45 mm, screw terminals integrated, monitoring of E-STOP, safety gates.

Technical details

General data

Approval: CE, CCC, UKCA, cULus Listed, KOSHA, EAC (Eurasian), TÜV

Technical data

Electrical data

Supply voltage (V): 110 - 110 V

Type of supply voltage U1: AC

Power consumption AC: 5 VA

Supply voltage 2 (V): 24 - 24 V

Type of supply voltage U2: DC

Inputs

Number of inputs: 2

Semiconductor outputs

Number of semicond. outputs: 1

Tolerance ext. volt. DC S/C: -20 %/+20 %

Utilisation cat. to EN 60947-1: DC-12

Relay outputs

Utilisation cat. AC/DC1 stand.: EN 60947-4-1

Voltage AC1 safety cont.: 240 V

Max. current AC1 safety cont.: 8 A

Voltage DC1 safety cont.: 24 V

Max. current DC1 safety cont.:	8 A
Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Voltage AC15 safety cont.:	230 V
Max. current AC15 safety cont.:	5 A
Voltage DC13 safety cont.:	24 V
Safety contacts: AC at UL:	240 VAC G. P.
Safety contacts: pilot duty:	B300, R300
Relay contact material:	AgSnO2
Addit. contact details relay:	+ 0.2 µm Au
Environmental data	
Climatic suitability to ...:	EN 60068-2-78
Ambient temperature:	-20 - 55 °C
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
EMC to standard ...:	EN 60947-5-1, EN 61000-6-2, EN 61326-3-1
Vibration to standard ...:	EN 60068-2-6
Clearance & creepage dist. to:	EN 60947-1
Overvoltage category:	III / II
Pollution degree clear.&creep.:	3
Mechanical data	
Mounting position:	any
Housing material front plate:	ABS UL 94 V0
Connection terminal:	Screw terminal
Terminal style:	fixed
Flex. cond. c/s AWG info:	24 - 10 AWG
Height dimension:	87 mm
Width dimension:	45 mm
Depth dimension:	121 mm
Net weight:	375 g

Gross weight:	385 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	7a, 7c I
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead, Lead oxide
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1, 1317-36-8
WEEE classification (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	0
Commercial data	
Harmonized System Code:	85364900
UNSPSC 25:	39122331
EAN-Code:	4046548011654
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371819
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000019
ETIM Reference Feature:	EC001449
Volume:	0.545 dm ³

Optional accessories

774090

COVER P-93

