



Part Number: 15324982

SINGLE WIRE SEAL FITS TO 6.7mm CAVITY

Attributes

Type: SINGLE WIRE SEAL

Outer Diameter (mm): 7.25

Borehole Diameter (mm): 1.6

Length (mm): 7.5

Min Cable Outer Diameter (mm): 2

Max Cable Outer Diameter (mm): 2.85

Color: GREEN

Hardness (Shore): 50

Contains Lubricant (Oil Content): Low

Restraint Ring: No

Min. operating temperature: -40°C

Max. operating temperature: +140°C