

VISTA TOUCH FLOW

Touch Screen Flow Rate Indicator and Totalizer

For use with Industrial Flow Meters























Graphic Display



Touchscreen



Built-in remote monitoring



Configuration Save and Export via USB flash drive*



2 Relay Outputs 1 Analog Output 2 Digital Inputs



Accuracy

- 0.1% accuracy across the input range
- 65K full color 70mm x 70mm [2.76" x 2.76"] graphics display
- Simple and intuitive touchscreen
- Fully configurable from the front panel
- Advanced alarm notifications
- Load and save configuration data to a USB flash drive*
- Free access to the IoT Trumeter Cloud remote monitoring with texts and emails alarm notifications
- Modbus® RTU and TCP*
- Industry standard 1/4 DIN mounting
- Ethernet and RS485 as standard*
- Modular pluggable quick connect/disconnect connectors

*Feature available 2024 via software update





Measurement Input

Input	Operating Range	Accuracy	Resolution	Frequency
Voltage	0V to +10V DC	0.1% of full scale	400uV	DC
Current	-50mA to +50mA	0.1% of full scale	2uA	DC
Pulse / Rate	Logic 0 = 0 to 0.6V DC	100PPM	1uSec	0 to 10KHz
	Logic 1 = 2.5V to 24V DC			

Power Supply

Mains Version 100-277VAC 50/60Hz 10W Low Voltage Version 12-24VAC/DC and 50/60Hz 10W

Communications, Networking and IoT

Modbus RTU **RS485** Modbus TCP Ethernet **Platform** Trumeter IoT Cloud

USB Mass storage (USB flash drive)

Control Inputs

2 x control input (12V to 277V AC/DC) Opto Isolated

Environmental

Operating Temperature Storage temperature Humidity

IP rating (from the front)

Shock Vibration Altitude

Installation Category **Pollution Degree**

-20°C to +60°C (-4°F to +140°F) -20°C to +70°C (-4°F to +158°F) 1% to 85% max non-condensing IP65, NEMA250 and UL50 Type12

20g to IEC68-2-27 5-500Hz, 2g up to 2000 meters

Ш 2

Memory

2MB of internal non-volatile memory to store all settings Supports USB flash drive (FAT16/FAT32 format up to 32GB)

Outputs

2 x Form C relay (277V AC / 5A Max | 30V DC / 5A Max) Relay

Analog 4-20mA Analog Output

24VDC Excitation voltage output (50mA Max)

Certifications

CE, UKCA, UL and cUL, EN61010-1

Display

Visible screen area Resolution

Brightness Contrast ratio Colors

Impact Resistance

Viewing angle Touch

Scratch Resistance

65 536 IK03 Toughened glass to EN62262 160° horizontally; 160° vertically

450cd/m²


800:1

480 x 480 pixels


Multi zone touch capacitive 6H to ASTM D4587


70mm x 70mm [2.76" x 2.76"]

Typical Application



Mechanical





Cut Out: 92mm x 92mm (3.62 "x 3.62") as per **DIN IEC 61554**

Part Numbers

VT-FLOW-LV VT-FLOW-HV VT-FLOW-XXX Vista Touch Flow Meter 12-24VAC/DC Vista Touch Flow Meter 100-277VAC Vista Touch Flow Meter Custom













Trumeter (The Americas) 6601 Lyons Rd, Suite H-7

Coconut Creek, Florida FL 33073,

Tel: +1 954 725 6699 Email: sales.usa@trumeter.com Trumeter (Europe)
Pilot Mill

Alfred Street Bury, BL9 9JR Tel: +44 161 674 0960 Email: sales.uk@trumeter.com

Innovative Design Technologies Sdn. Bhd Lot 5881, Lorong Iks Bukit Minyak 1 Taman Perindustrian Iks, 14000 Bukit Tengah Penang, Malaysia Web: www.idtworld.com

Tel: + 604 5015700 Email: sales.my@idtworld.com