

• APTIV •



Part: 15300027

2 Way 2.8 M/P 280 Sealed

Attributes

Product Family: Metri-Pack

Product Series: 280 Series

Max. operating temperature: +125°C

Min. operating temperature :-40°C

No. of Ways: 2

Cable Exit Orientation: 180°

Gender: Female

Length (mm): 25.2

Width (mm): 29.9

Height (mm): 25

Color: BLACK

Primary Locking Mechanism: CAVITY LOCK

Weight (g): 3.69792

Terminal 1 Size: 2.8

Sealing: Sealed

Primary Material: PA 66